


PLANACON™ PHOTOMULTIPLIER TUBE ASSEMBLY 85011-501

BURLE

PRELIMINARY
October 2003

The 85011 assembly is based on a new photomultiplier tube that uses microchannel plates (MCP) for electron multiplication, the PLANACON™. This 2" square head-on MCP-PMT is very low profile, less than one inch thick including the voltage divider network. The sixty-four anodes provide 6mm position resolution when used as a discrete pixel device. Improved resolution can be obtained using the charge-sharing technique with an alternate voltage divider network. The dual MCP multiplier provides excellent time response, good gain, and extremely high pulse linearity. Response uniformity over the full 2" square active area is exceptional, typically 1:1.5. The assembly comes with terminated anode and high voltage cables for ease of use. Applications include specialized medical imaging, ring imaging Cherenkov counters, fluorescence microscopy, and high-speed applications such as LIDAR.



GENERAL

Parameter		Value	Unit
Spectral Response		165 to 660	nm
Wavelength of Maximum Response		410	nm
Photocathode Material		Bialkali	--
Window	Material	Quartz	--
	Thickness	0.080	in
Multiplier	Structure	MCP (25µm pore, 40:1 L:D)	--
	Number of Stages	2	--
Anodes	Number	64 (8 x 8)	
	Size / Pitch	0.234 / 0.254	in
Voltage Divider Resistance		12	MΩ

Maximum Ratings (Absolute Maximum Values)

Parameter		Value	Unit
Supply Voltage	Between Anode and Cathode	2400	Vdc
Average Anode Current, sum of all anodes		3	µA
Ambient Temperature		- 40 to + 50	C



Characteristics (at 25 °C)


Parameter		Min.	Typ.	Max.	Unit
Cathode Sensitivity	Luminous	40	55	--	μA/Lm
	Blue (with CS-5-58 filter)	5.5	7.5	--	μA/lm-b
Anode Sensitivity	Luminous		35	--	A/lm
Modal Gain		0.3×10^6	0.6×10^6	--	--
Anode Dark Current, Sum of all pixels		--	0.5	5	nA
Time Response	Anode Pulse Rise Time	--	0.3	--	ns
	Anode Pulse Width (FWHM)	--	1.8	--	ns
Pulse Linearity at 5% Deviation		--	300	--	mA
Single Electron Response	Peak-to-Valley	--	2:1	--	
	Resolution (FWHM)	--	150	--	%
Anode Uniformity		--	1:1.25	1:1.5	
Pulse Height Resolution, 2" NaI(Tl) crystal, ¹³⁷ Cs, 1700V (FWHM)		--	10.0	--	%

Note: Measured with the condition shown in Table 1 except where noted.

Table 1 VOLTAGE DISTRIBUTION RATIO AND SUPPLY VOLTAGE (-2300 Volts)

Electrodes	K	MCP _{in}	MCP _{out}	P
Ratio	1	10	1	

Supply Voltage: 1000Vdc, K : Cathode P : Anode



The information furnished is believed to be accurate and reliable, but is not guaranteed and is subject to change without notice. No liability is assumed by BURLE INDUSTRIES for its use. Performance data represents typical characteristics and not specifications as actual, individual product performance may vary. Customers should verify that they have the most current BURLE product information before placing orders, and should independently test and evaluate BURLE products for their intended use. No claims or warranties are made as to the application of BURLE products or their suitability or fitness for any particular purpose. This document may not be reproduced, in whole or in part, without the prior written consent of BURLE INDUSTRIES.

Copyright 2003 by BURLE Technologies, Inc. All rights reserved.

BURLE® and BURLE INDUSTRIES® are registered trademarks of BURLE Technologies, Inc. Marca(s) Registrada(s). Printed in the U.S.A.

FOR ADDITIONAL INFORMATION, TELEPHONE IF IN THE U.S.A. OR CANADA 1-800-366-2875, AND ELSEWHERE, 1-717-295-6888, OR FAX REQUEST TO 1-717-290-1263. BURLE INDUSTRIES, INC., 1000 New Holland Avenue, Lancaster, Pennsylvania 17601-5688 U.S.A.